

3mm diameter, single and dual stage



DATASHEET





The OITS Series 1310/1550 Twin Optical Isolator integrates two independent isolators into one compact package to save space and cost. Each isolator guides light at 1310 or 1550 nm in the normal direction while minimizing back reflection and back scattering in the reverse direction for any state of polarization. Employing Agiltron's proven advanced micro optics design, it features low insertion loss, high isolation, compact structure, and high stability. These Telcordia qualified components have excellent characteristics, making them an ideal choice for application in fiber amplifier systems, pump laser diodes, and optical fiber sensors.

Features

- Low Insertion Loss
- High Isolation
- Low PDL
- High Reliability
- Low Cost

Applications

- Optical Fiber Amplifier
- Pump Laser Source
- Fiber Optic Sensor
- Instrumentation

Specifications

Parameter	Min	Typical	Max	Unit		
	1310		1310 ± 20		nm	
Operation Wavelength (λο)	C Band		1550 ± 20			
	L Band		1585 ± 20			
Insertion Loss (Over Le 22°C)	Single Stage		0.5	0.75	dB	
Insertion Loss (Over λο, 23°C)	Dual Stage		0.6	0.9	ав	
Isolation (Over λο, 23°C)	Single Stage	28	30	35	dB	
	Dual Stage	40	43	50		
Deal Indiation (Over 3 - 22%)	Single Stage	38	35	40	dB	
Peak Isolation (Over λο, 23°C)	Dual Stage	48	50	55		
Directivity (Over λο, 23°C)	55			dB		
Crosstalk (Over λο, 23°C)		50	55		dB	
Polarization Dependent Loss (Over λο & To)			≤ 0.15		dB	
Polarization Mode Dispersion (Ov		≤ 0.2		ps		
Return Loss (Over λο & To, Input/Output)		55 / 55			dB	
Operating Temperature	-5		+70	°C		
Storage Temperature	-40		+85	°C		
Optical Power Handling		≤ 400		mW		

Note: The specifications provided are for general applications with a cost-effective approach. If you need to narrow or expand the tolerance, coverage, limit, or qualifications, please [click this link]:


Warning: This is an OEM module designed for system integration. Do not touch the PCB by hand. The electrical static can kill the chips even without a power plug-in. Unpleasant electrical shock may also be felt. For laboratory use, please buy a Turnkey system.

Legal notices: All product information is believed to be accurate and is subject to change without notice. Information contained herein shall legally bind Agiltron only if it is specifically incorporated into the terms and conditions of a sales

Rev 06/12/24

© Photonwares Corporation

P +1 781-935-1200








3mm diameter, single and dual stage



DATASHEET

Mechanical Dimensions (mm)



Ordering Information

Prefix	Туре	Wavelength	Grade	Package	Fiber Type	Fiber Cover	Fiber Length	Connector
OITS-	Single Stage = 12 Dual Stage =22	1310 = 3 C Band = C L Band = L Special = 0	Standard = 1 Special = 0	Ø5.5x34 = 1 Ø3x30 = 2 Special = 0	SMF-28 = 1 Special = 0	Bare Fiber = 1 900µm Loose Tube = 3 Special = 0	0.25m = 1 0.5m = 2 1.0m = 3 Special = 0	None = 1 FC/PC = 2 FC/APC = 3 SC/PC = 4 SC/APC = 5 ST/PC=6 LC/PC=7 LC/APC= A LC/UPC = U Special=0

Application Notes

Fiber Core Alignment

Note that the minimum attenuation for these devices depends on excellent core-to-core alignment when the connectors are mated. This is crucial for shorter wavelengths with smaller fiber core diameters that can increase the loss of many decibels above the specification if they are not perfectly aligned. Different vendors' connectors may not mate well with each other, especially for angled APC.

Fiber Cleanliness

Fibers with smaller core diameters (<5 µm) must be kept extremely clean, contamination at fiber-fiber interfaces, combined with the high optical power density, can lead to significant optical damage. This type of damage usually requires re-polishing or replacement of the connector.

Maximum Optical Input Power

Due to their small fiber core diameters for short wavelength and high photon energies, the damage thresholds for device is substantially reduced than the common 1550nm fiber. To avoid damage to the exposed fiber end faces and internal components, the optical input power should never exceed 20 mW for wavelengths shorter 650nm. We produce a special version to increase the how handling by expanding the core side at the fiber ends.

^{*}Product dimensions may change without notice. This is sometimes required for non-standard specifications.





3mm diameter, single and dual stage




DATASHEET

Typical Wavelength Dependence for Single Stage







© Photonwares Corporation

P +1 781-935-1200

E sales@photonwares.com

w www.agiltron.com



3mm diameter, single and dual stage



DATASHEET

Typical Wavelength Dependence for Dual Stage

