


Double-Clad Fiber Coupler

(efficient collecting back reflection lights)



DATASHEET

BUY NOW 



The List of the Links to the Datasheet Files:

[Double-Clad Fiber Coupler 430nm to 680nm](#)

[Double-Clad Fiber Coupler 680nm to 980nm](#)

[Double-Clad Fiber Coupler 960nm to 1260nm](#)

[Double-Clad Fiber Coupler 1250nm to 1550nm](#)

Features

- Single Mode Core Guide
- Multimode Reflection Guide
- Low Loss Transmission
- High Efficient Collection
- Versatile

Applications

- LiDAR
- OCT
- Fluorescence Imagine
- Confocal Microscopy
- Endoscopy

Legal notices: All product information is believed to be accurate and is subject to change without notice. Information contained herein shall legally bind Agiltron only if it is specifically incorporated into the terms and conditions of a sales agreement. Some specific combinations of options may not be available. The user assumes all risks and liability whatsoever in connection with the use of a product or its application.

Rev 01/30/24